

## PLK-G Series Spare Parts List

Description	All 1010 Models	2516	4030-6030	5050-10050
NEEDLE PLATE 2.2mm (Standard for size 18-20 Needle)	ME10A1101	→	→	→
NEEDLE PLATE 2.6mm (For size 21-22 Needle)	ME10A2101	→	→	→
NEEDLE PLATE 3.0mm (Tapered Hole) (For size 23 Needle)	ME10A5101	→	→	→
NEEDLE PLATE SPACER	MS01A1476	→	→	→
SCREW FOR NEEDLE PLATE	M90605010	→	→	→
LARGE SHUTTLE HOOK	MA10A0120	→	→	→
HOOK DRIVER	MS01A0611	→	→	→
OUTER HOOK RETAINER	MS01A0616	→	→	→
BOBBIN FOR LARGE HOOK	MA10A0123	→	→	→
BOBBIN CASE FOR LARGE HOOK	MS17A0125	→	→	→
THREAD GUIDE ABOVE HOOK	MS01A0329	→	→	→
SCREW FOR THREAD GUIDE	M90853002	→	→	→
MOVEABLE KNIFE	MS03B0838	→	→	→
SCREW FOR MOVABLE KNIFE	M91129015	→	→	→
WAVE WASHER FOR MOVABLE KNIFE	M96004052	→	→	→
FIXED KNIFE	MS14A0838	→	→	→
FIXED KNIFE SPACER	MA10B2476	→	→	→
SCREW FOR FIXED KNIFE	M90906003	→	→	→
PRESSER FOOT STANDARD (3mm Diameter)	MV30A0256	→	→	→
PRESSER FOOT (2mm Diameter)	MV30A1256	→	→	→
PRESSER FOOT LONG BARREL (3mm Diameter)	MA35A0256	→	→	→
PRESSER FOOT LONG BARREL (2mm Diameter)	MA35A1256	→	→	→
SCREW FOR PRESSER FOOT	M90922002	→	→	→
NEEDLE THREAD GUIDE ON NEEDLE BAR	MF21D0181	→	→	→
NEEDLE THREAD GUIDE ON NEEDLE BAR BUSHING	MF01A0181	→	→	→
NEEDLE SET SCREW	M90815002	→	→	→
CHECK SPRING	MF10A0187	→	→	→
TENSION RELEASE CABLE	None	None	ME40E0746	→
Y-AXIS HOMING SENSOR	MH10A2501	MH27E2484	MH40E2484	ME50A1484
X-AXIS HOMING SENSOR	MH10A1501	→	MH40E1484	ME50A0484
PRESSER FOOT SENSOR	MH10A0501	MH25A0484	MH40E0484	→
WIPER	MH10A0980	→	MA20A0980	→
WIPER SCREW	M90806002	→	M91057020	→