

RF System BIS-V (DP) read	Speed Test		256 bytes
	126 bytes/cycle		3
	PLC Scan	8ms	Fieldbus scan 10ms
	Cycles Tested:		1000
	BIS0130		BIS00T0
	min		322.3
	max		401.283
	write		
	min		558.765
	max		641.317

BIS-V (PN) read	Speed Test		252 bytes/cycle	2
	8ms		Fieldbus scan 2ms	
	PLC Scan	8ms	Fieldbus scan 2ms	
	Cycles Tested:		1000	
	BIS0130		BIS00T0	
	min		204.193	
	max		240.553	
	Write			
	min		459.672	
	max		495.771	

	Speed Test		1024 bytes
	126 bytes/cycle		9
	PLC Scan	8ms	Fieldbus scan 10ms
	Cycles Tested:		500
	BIS0130		BIS00T0
	min		774.972
	max		876.697
	min		1713.579
	max		1805.709

	Speed Test		252 bytes/cycle	5
	8ms		Fieldbus scan 2ms	
	PLC Scan	8ms	Fieldbus scan 2ms	
	Cycles Tested:		500	
	BIS0130		BIS00T0	
	min		656.542	
	max		693.972	
	min		1619.332	
	max		1649.802	

BIS-M (DP) Read	Speed Test		256 bytes
	126 bytes/cycle		3
	PLC Scan	8ms	Fieldbus scan 10ms
	Cycles Tested:		
	BIS0053		
	min		381.151
	max		427.21
	Write		
	min		822.802
	max		862.259

	Speed Test		1024 bytes
	126 bytes/cycle		9
	PLC Scan	8ms	Fieldbus scan 10ms
	Cycles Tested:		500
	BIS0053		
	min		959.036
	max		1053.81
	min		2766.28
	max		2825.978

BIS-M (PN)read	Speed Test		256 bytes
	250 bytes/cycle		2
	PLC Scan	8ms	Fieldbus scan 2ms
	Cycles Tested:		1000
	BIS0053		
	min		581.447
	max		865.422
	Write		
	min		1250.476
	max		1506.928

	Speed Test		1024 bytes
	250 bytes/cycle		5
	PLC Scan	8ms	Fieldbus scan 2ms
	Cycles Tested:		500
	BIS0053		
	min		1948.779
	max		2198.082
	min		4620.75
	max		4878.88

Read	Speed Test		256 bytes
	8 bytes/cycle		32
	PLC Scan	3ms	Fieldbus scan 16ms
	Cycles Tested:		28000
	min		2044.776
	max		2446.332
	Write		
	min		3755.843
	max		3886.419

	Speed Test		256 bytes
	8 bytes/cycle		32
	PLC Scan	3ms	Fieldbus scan 4ms
	Cycles Tested:		32
	min		1451.254
	max		1701.323
	min		3254.645
	max		3804.94