

MELSEC-L Series Power Supply

Power Supplies

Model Number	L61P (*1)	L63P	L63SP
Stocked Item	S	S	S
Certification	UL • cUL • CE		
Input Power Supply	100 to 240 VAC (-15% to +10%)	24 VDC (-35% to +30%)	24 VDC (-35% to +30%)
AC Supply Frequency	50/60Hz (-5% to +5%)	-	-
AC Supply Voltage Distortion Factor	Within 5%	-	-
Maximum Input Apparent Power	130 VA	-	-
Maximum Input Power	-	45W	45W
Inrush Current	≤8ms @ 20A	≤1ms @ 100A (for 24 VDC input)	100A within 1ms (24 VDC input)
Rated Output Current (5VDC)	5A		
Allowable Momentary Power Failure Time	10ms	10ms (24 DC input)	Within 10ms (24 VDC input)
Weight (kg)	0.32	0.29	0.19
Dimensions (W x H x D) mm	45 x 90 x 95		29 x 90 x 95

Note 1: AC Power Supply included in CPU sets; L02CPU-SET, L06CPU-SET, L26CPU-SET, and L26CPU-BT-SET