

Simple Motion Module FX5-40SSC-S/FX5-80SSC-S for FX5 PLC Parts List

Model Number	Description	Stocked Items
FX5-40SSC-S	4 Axis Simple Motion Module for FX5 with SSCNETIII/H	S
FX5-80SSC-S	8 Axis Simple Motion Module for FX5 with SSCNETIII/H	S
Cables and Accessories		
MR-ECN1	External I/O Signal Connector	S
MR-HDP01	Manual pulse generator, Pulse resolution: 25PLS/rev(100PLS/rev after magnification by 4). Permitted speed: 200r/min	S
LD77DOCBL-2M	Differential Output Type Cable for External I/O - 2 Meter	S
LD77DOCBL-5M	Differential Output Type Cable for External I/O - 5 Meter	S
LD77DOCBL-10M	Differential Output Type Cable for External I/O - 10 Meter	S
LD77DOCBL-20M	Differential Output Type Cable for External I/O - 20 Meter	-
LD77DOCBL-30M	Differential Output Type Cable for External I/O - 30 Meter	-
LD77OCCBL-2M	Voltage Output/Open Collector Cable for External I/O - 2 Meter	S
LD77OCCBL-5M	Voltage Output/Open Collector Cable for External I/O - 5 Meter	S
LD77OCCBL-10M	Voltage Output/Open Collector Cable for External I/O - 10 Meter	S
MR-TBNATBL05M	0.5M I/O Interface Terminal Block Cable	S
MR-TBNATBL1M	1M I/O Interface Terminal Block Cable	S
MR-TB26A	Junction Terminal Block	S