

Networking Modules

Ethernet Interface Module

Model Number	WS0-GETH00200		
Stocked Item	S		
Certification	UL • cUL • CE		
Number of Modules Mountable to the Safety Controller	Max. 2 modules (in total WS0-GETH and WS0-GCC1)		
Communication	Network Type	Ethernet (TCP/IP) 100Base-TX	Ethernet (TCP/IP) 10Base-T
	Transmission Rate	100Mbps	10Mbps
	Connection Technique	RJ45	
Number of Connections	Max. 4 connections + 1 connection (for Setting and Monitoring Tool only)		
Enclosure Rating (EN/IEC 60529)	IP20		
Internal Power Consumption (W)	Max. 2.4		
Weight (g)	125		
Dimensions (W x H x D) mm	22.5 x 96.5 x 121		

CC-Link Interface Module

Model Number	WS0-GCC100202		
Stocked Item	S		
Certification	UL • cUL • CE		
Number of Modules Mountable to the Safety Controller	Max. 2 modules (in total WS0-GETH and WS0-GCC1)		
CC-Link Station Type	Remote device station		
CC-Link Version	Ver. 1.10		
Data Transmission Speed	156kbps/625kbps/2.5Mbps/5Mbps/10Mbps (autosensing)		
Station Number	1 to 64 (factory default: 0)		
Number of Occupied Stations	1 station (RX/Ry 32 points each, RWw/RWr 4 points each) 2 stations (RX/Ry 64 points each, RWw/RWr 8 points each) 3 stations (RX/Ry 96 points each, RWw/RWr 12 points each) 4 stations (RX/Ry 128 points each, RWw/RWr 16 points each) (The last 16 points of RX/Ry are for system use (reserved))		
Cable	Ver. 1.10-compatible CC-Link dedicated cable (*1)		
Housing Enclosure Rating / Terminals	IP40/IP20 according to IEC 60529		
Weight (g)	120		
Dimensions (W x H x D) mm	22.5 x 96.5 x 120.8		

Note 1: Connect a terminating resistor (110Ω).