

GOT2000 Option Units

Product Name	Model Number	Specifications	GT27	GT25	GT21	Stk Item
Printer Unit	GT15-PRN	USB slave (PictBridge) for printer connection, 1ch. Cable for printer connection (3m) included	X	X (*4)	-	S
Multimedia Unit	GT27-MMR-Z	For video input (NTSC/PAL), 1 channel, recording video/playing video files (A set of GT16M-MMR-Z and GT27-IF1000)	X (*1)	-	-	S
Video Input Unit	GT27-V4-Z	For video input (NTSC/PAL), 4 channels (A set of GT16M-V4-Z and GT27-IF1000)	X (*1)	-	-	S
Digital Video Output Unit	GT27-VHOUT	For HDMI output 1 ch	X (*1)	-	-	S
RGB Input Unit	GT27-R2	For analog RGB input, 2 channels (Simultaneous display) (*3)	X (*1)	-	-	S
Video/RGB Input Unit	GT27-V4R1-Z	For video input (NTSC/PAL) 4ch / analog RGB 1ch input	X (*1)	-	-	S
RGB Output Unit	GT27-ROUT	For analog RGB output 1ch	X (*1)	-	-	S
Sound Output Unit	GT15-SOUT	For sound output (Φ3.5 stereo pin jack)	X	X (*4)	-	S
External Input/Output Unit	GT15-DIOR	For connecting an external I/O device and an operation panel (Negative common input, source type output)	X	X (*4)	-	-
	GT15-DIO	For connecting an external I/O device and an operation panel (Positive common input, sink type output)	X	X (*4)	-	S
SD Memory Card Unit	GT21-03SDCD	For SD card mounting	-	-	X (*2)	S

Notes:

1. Not available to GT2705.
2. Available to GT2103-PMBD, GT2103-PMBDS, and GT2103-PMBDS2.
3. The settings for GT27-R2 and GT27-R2-Z differ in the screen design software.
4. Not available to GT2510-WXTBD, GT2510-WXTSD, GT2507-WTBD, and GT2507-WTSD.

GOT2000 Series Options and Accessories

Product Name	Model Number	Specifications	GT27	GT25	GT21	Stk Item		
Protective Sheet (*1)	GT27-15PSGC	For 15" screens	X	-	-	S		
	GT25-12PSGC	For 12.1" screens	X	X	-	S		
	GT25-10PSGC	For 10.4" screens	X	X	-	S		
	GT25-08PSGC	For 8.4" screens	X	X	-	S		
	GT25-05PSGC	For 5.7" screens	X	-	-	S		
	GT25-05PSGC-2	For 5.7" screens	-	X	-	S		
	GT25-10WPSGC	For 10.1" wide	• Antiglare type • Transparent • Hole for the USB environmental protection cover • Set of 5 sheets	-	X	-	S	
	GT21-07WPSGC	For 7" wide screens	• Antiglare type • Transparent • No hole for the USB environmental protection cover *10 • Set of 5 sheets	-	X	X	S	
	GT27-15PSCC	For 15" screens		X	-	-	S	
	GT25-12PSCC	For 12.1" screens		X	X	-	S	
	GT25-10PSCC	For 10.4" screens	• Clear type • Transparent • Hole for the USB environmental protection cover • Set of 5 sheets	X	X	-	S	
	GT25-08PSCC	For 8.4" screens	• Clear type • Transparent • Hole for the USB environmental protection cover • Set of 5 sheets	X	X	-	S	
	GT25-05PSCC	For 5.7" screens		X	-	-	S	
	GT25-05PSCC-2	For 5.7" screens		-	X	-	S	
	GT25-10WPSCC	For 10.1" wide	• Clear type • Transparent • No hole for the USB environmental protection over *10 • A set of 5 sheets	-	X	-	S	
	GT21-07WPSCC	For 7" wide screens	• Clear type • Transparent • No hole for the USB environmental protection over *10 • A set of 5 sheets	-	X	X	S	
	GT25-12PSCC-UC (*9)	For 12.1" screens		X (*9)	X	-	S	
	GT25-10PSCC-UC (*9)	For 10.4" screens	• Clear type • Transparent • No hole for the USB environmental protection cover *2 • Set of 5 sheets	X (*9)	X (*9)	-	S	
	GT25-08PSCC-UC (*9)	For 8.4" screens		X	X (*9)	-	S	
	GT25F-12ESGS	For 12.1" screens	• For conforming to IP67F • Antiglare type	-	X (*7)	-	S	
	GT25F-10ESGS	For 10.4" screens	• Silvery	-	X (*7)	-	S	
	GT25F-08ESGS	For 8.4" screens	• 1 sheet	-	X (*7)	-	S	
	GT21-04RPSGC-UC	For 4.3" wide screens	• Antiglare type • Transparent • No hole for the USB environmental protection cover • Set of 5 sheets	-	-	X	S	
	GT21-03PSGC-UC	For 3.8" screens		-	-	X	S	
	GT21-03PSCC-UC	For 3.8" screens	• Clear type • Transparent	-	-	X	S	
	GT21-04RPSCC-UC	For 4.3" screens	• No hole for the USB environmental protection cover • Set of 5 sheets	-	-	X	S	
	GT21-05PSGC	For 5.7" screens	• Antiglare type • Transparent • Hole for the USB environmental protection cover • Set of 5 sheets	-	-	X	S	
	GT21-05PSCC		• Clear type • Transparent • Hole for the USB environmental protection cover • Set of 5 sheets	-	-	X	S	
	GT21-07WPSGC	For 7" screens	• Antiglare type • Transparent • No hole for the USB environmental protection cover *10 • Set of 5 sheets	-	-	X	S	
	GT21-07WPSCC		• Clear type • Transparent • No hole for the USB environmental protection cover *10 • Set of 5 sheets	-	-	X	S	
UV Protective Sheet	GT25T-07WPSVC	For 7" rugged		• Antiglare type (UV cutoff) • Transparent • 1 sheet	-	X	-	S
USB Environmental Protection Cover	GT25-UCOV	For 15"/12.1"/10.4"/8.7" Protective cover for USB interface on GOT front panel (for replacement)	X	X	-	S		
	GT25-05UCOV	For 5.7" Replacement USB Env. Cover GT2705 Series	X	-	-	S		
	GT21-WUCOV	Replacement USB cover for 10.1", 7", 5.7" (GT25/21 Wide Series)	-	X	X	S		
Protective Cover for Oil (*3)	GT25-05PCO	For 5.7" screens	X	-	-	S		
	GT25T-07WPCO	For 7" rugged	-	X	-	S		
	GT20-15PCO	For 15" screens	X	-	-	S		
	GT20-12PCO	For 12.1" screens	X	X	-	S		
	GT20-10PCO	For 10.4" screens	X	X	-	S		
	GT20-08PCO	For 8.4" screens	X	X	-	S		
	GT21-04RPCO	For 4.3" Wide screens	-	-	X	S		
	GT10-20PCO	For 3.8" screens	-	-	X	S		
Stand	GT15-90STAND	For 15" screens	X	-	-	-		
	GT15-80STAND	For 12.1" screens	X	X	-	-		
	GT15-70STAND	For 10.4"/8.4" screens	X	X	-	-		
	GT05-50STAND	For 5.7" screens	X	X	-	-		

Notes: See notes next page.

GOT2000 Series Options and Accessories (continued)

Product Name		Model Number	Specifications	Applicable Model			Stocked Item
				GT27	GT25	GT21	
Memory Card	SD Card	NZ1MEM-2GBSD	2GB SD memory card for GOT	X	X	X	S
		NZ1MEM-4GBSD	4GB SDHC memory card for GOT	X	X	X	S
		NZ1MEM-8GBSD	8GB SDHC memory card for GOT	X	X	X	S
		NZ1MEM-16GBSD	16GB SDHC memory card for GOT	X	X	X	-
	CF Card	GT05-MEM-128MC	128MB CF card for GT27-MMR-Z	X	-	-	-
		GT05-MEM-256MC	256MB CF card for GT27-MMR-Z	X	-	-	-
		GT05-MEM-512MC	512MB CF card for GT27-MMR-Z	X	-	-	-
		GT05-MEM-1GC	1GB CF card for GT27-MMR-Z	X	-	-	-
		GT05-MEM-2GC	2GB CF card for GT27-MMR-Z	X	-	-	-
		GT05-MEM-4GC	4GB CF card for GT27-MMR-Z	X	-	-	-
Memory Card Adapter	GT05-MEM-16GC	16GB CF card for GT27-MMR-Z	X	-	-	-	
	GT05-MEM-ADPC	CF card memory card (TYPE II) conversion adapter for GT27-MMR-Z	X	-	-	-	
Attachment	GT15-70ATT-98	For 10.4"	For conversion from GT168_, GT158_, A985GOT (*4)	X	X	-	-
	GT15-70ATT-87		For conversion from A870GOT-SWS/TWS, A8GT-70GOT-TB/TW/SB/SW	X	X	-	S
	GT15-60ATT-97	For 8.4"	For conversion from GT167_, GT157_, A97MGOT	X	X	-	S
	GT15-60ATT-96		For conversion from A960GOT	X	X	-	S
	GT15-60ATT-87		For conversion from A870GOT-EWS, A8GT-70GOT-EB/EW, A77GOT-EL, A77GOT-EL-S5/S3	X	X	-	S
	GT15-60ATT-77	For 5.7"	For replacing A77GOT-CL, A77GOT-CL-S5/S3, A77GOT-L, A77GOT-L-S5/S3	X	X	-	-
	GT15-50ATT-95W		For replacing A956WGOT, F940WGOT	X	-	-	S
	GT15-50ATT-85	For replacing A85_GOT	X	-	-	S	
GT21-04RATT-40	For 4.3"	For replacing GT104_	-	-	X (*8)	S	
Battery	GT11-50BAT	Battery for backup of SRAM data, clock data, and system status log data (included with GT27 and GT25) (*6)		X (for replacement)	X (for replacement)	X (*5) (for replacement)	S
Misc	GT2103-MOUNT-K	GT2103-PMBD Mounting Kit		-	-	X	S
	GT2103S-MOUNT-K	GT2103-PMBDS/S2/LS Mounting Kit		-	-	X	S
	GT2104-MOUNT-K	GT2104 Mounting Kit		-	-	X	S
	GT2105-MOUNT-K	GT2105 Mounting Kit		-	-	X	S
	GT2505-MOUNT-K	GT2505 Mounting Kit		-	X	-	S
	K01H70500292	GT21/GT25 Wide Mounting Hardware (4 pieces)		-	X	X	S
	GT21-04RATT-40	Adjuster Between GT104 & GT2104		-	-	X	S
	D808D197G53	GT27/GT25 Series Mounting Hardware (4 pieces)		X	X	-	S
	GT25-10FIT-EXS	GOT 2000 series fittings to be conformed with ATEX/KCs		X	X	-	S
GT25-12FIT-EXS	GOT 2000 series fittings to be conformed with ATEX/KCs		X	X	-	S	

Notes:

1. The white model does not have the front USB interface. It is recommended to use the products that the USB environmental protection cover area is closed.
2. When using the product with the USB environmental protection cover area closed, the front USB interface cannot be used.
3. Check if the protective cover for oil can be used in the actual environment before use. When using the cover, the front USB interface and human sensor cannot be used.
4. Including the GP250_ and GP260_ manufactured by Digital Electronics Corporation.
5. GT2103 does not have a built-in battery.
6. GT21 does not support the system status log data backup function.
7. GT2512F, GT2510F, GT2508F only.
8. Only available to GT2104-RTBD.
9. Necessary for the GOT to comply with the ATEX directive and KCs regulation. For applicable GOT models, contact your local sales office.
10. The protective sheet is shaped not to cover the USB environmental protection cover.