

GT1562/GT1565

HUMAN MACHINE INTERFACES



Modern Functionality

- Innovative Alarming, Messaging and Recipe Management
- Multi-Channel Communication Functions
- Multilevel Security protection
- Graphical Trending, Data Sampling and Time Scheduling Functions
- Advanced Data Sharing and Gateway Functions (FTP, Email, Client/Server functions)
- Handy Scripting Functions

Maintenance and Utility

- Advanced Maintenance and Diagnostics
- Transparent Mode Functions
- Preventative Maintenance
- Expandable Project Memory and Upgradeable OS

Performance and Design


- Ultra-compact design
- Ultra-wide viewing angles
- High Speed 64bit Super Scalar RISC processor
- Mitsubishi Graphics Accelerator
- Communication Option Slots and Embedded Power Supply

Convenience

- Front Panel Mounted USB Port
- Compact Flash Expansion Slot
- Multi language (Unicode 2.1) and True Type Font support



Model	GT1562-VNBA (D)	GT1565-VTBA(D)
Display type	TFT	
Display size	8.4"	
Resolution	(VGA) 640*480	
Colors	16	256/65K
Input type	Touch	
Touch Areas (points)	1200	
Processor	64bit RISC Processor + MGA (Mitsubishi Graphic Accelerator)	
FLASH memory	5MB (Up to 53MB with Expansion Memory)	9MB (Up to 57MB with Expansion Memory)
Serial ports	RS232 (9-pin DSUB)	
USB Port Device	One Port for 12MB Project Transfer/Transparent Programming Monitoring	
Memory cards	One external Compact Flash (CF) slot	
Real-time clock	Battery backed	
Power supply	100-240VAC (24VDC)	
Dimensions (W x H x D) mm	241 x 190 x 52	
Panel Cutout (W x H) mm	227 x 176	
Weight (kg)	1.8	



Unit: mm (inch)

Mitsubishi Electric Automation, Inc.
500 Corporate Woods Parkway
Vernon Hills, IL 60061
Phn: (847) 478-2100
Fax: (847) 478-2253

Mitsubishi Electric Automation, Inc.
4299 14th Avenue
Markham, Ontario L3R 0J2
Phn: (905) 475-8989
Fax: (905) 475-7935

Visit us at www.meau.com

Effective February, 2006 • L-VH-06062
Specifications subject to change without notice.