

E1032

HUMAN MACHINE INTERFACES



- Compact industrial construction
- Built-in and configurable serial ports (RS232/RS422/RS485*)
- Expansion option slots
- Real time clock
- Upgradeable terminal firmware and communication drivers
- Programmable function keys
- Programmable multicolored LEDs
- Removable text strips
- Ultra-thin display panel construction
- High resolution display technology
- Built-in 10/100MB Ethernet ports
- Universal Serial Bus (USB) ports (host support)

E1032 General Specifications

Display Type	STN
Display Size	5.4"
Resolution/Pixels	240 x 64
Colors	Monochrome (Black and White)
Input Type	Keypad
LED / Function Keys	20 / 22
Alarm Function	7 – 11 groups
RAM Memory	64 MB SDRAM
FLASH Memory	12 MB
Serial Ports	RS232 (9-pin DSUB), combined RS422/RS485 (25-pin DSUB)
Ethernet	One 10/100 Mbit TP-port
USB Host	One port for printer, keyboard, mouse, scanner. . .
Memory Cards	Not available
Real-Time Clock	Battery backed
Housing / Front Material	Cast aluminum
Power Supply	±24 VDC (20 - 30 VDC)
Dimensions mm (inches)	202 x 187 x 6 (8.0 x 7.4 x 0.2)
Weight kg (lbs)	0.875 (1.9)
Max. Current Draw Min. (Max.)	0.15 (0.35)
Ambient Temp V (H)	0 – 50°C (0 – 40°C)

